

LA granular activated carbon (GAC)

WORKING CONDITIONS

Max working temperature _____45°C (113°F) Min working temperature _____4°C (39,2°F)

SPECIFICATIONS

Non-toxic materials, suitable for drinking water. Container, end cap and grid: polypropylene. Flat seal SX: SEBS with antimicrobial technology. O-rings BX: EPDM.

Containing sponge: polyurethane.

Treatment material: granular activated carbon from coconut shell.

Plastic container filled with GAC, made from coconut shell for the reduction of chlorine, taste, odour (CTO) and volatile organic compounds (VOC), designed to provide the highest contact time of the water through the whole GAC bed. LA cartridges are available with height from 5" to 20".

LA SX

| GRANULAR A | CTIVATED CARBON WITH DOUBLE OPEN END (DOE) | | | | | |
|------------|--|---------|---------------|---------------|----|----|
| CODE | MODEL | NOMINAL | RECOMMENDED | DIMENSIONS MM | | |
| | | HEIGHT | FLOW RATE I/h | Α | В | C |
| | OD 1,77" x ID 0,71" | | | | | |
| RA5180125 | LA MIGNON SX | 5" M | 150 | 125 | 50 | 21 |
| | OD 2,40" x ID 1,10" | | | | | |
| RA5182125 | LA 5 SX | 5" | 200 | 128 | 70 | 28 |
| RA5184125 | LA 7 SX | 7" | 300 | 176 | 70 | 28 |
| RA5185125 | LA 10 SX | 10" | 500 | 252 | 70 | 28 |
| RA5187125 | LA 20 SX | 20" | 750 | 510 | 70 | 28 |
| | | | | | | |

LA BX


| <u>Granular a</u> | CTIVATED CARBON WITH DOUBLE O RING COLLAR 45 MM | | | | | |
|-------------------|---|---------|---------------|---------------|----|----|
| CODE | MODEL | NOMINAL | RECOMMENDED | DIMENSIONS MM | | |
| | | HEIGHT | FLOW RATE I/h | Α | В | С |
| | OD 2,40" x ID 1,10" | | | | | |
| RA5182225 | LA 5 BX | 5" | 200 | 127 | 70 | 25 |
| RA5184225 | LA 7 BX | 7" | 300 | 183 | 70 | 25 |
| RA5185225 | LA 10 BX | 10" | 500 | 252 | 70 | 25 |
| RA5187225 | LA 20 BX | 20" | 750 | 510 | 70 | 25 |


Reduction of: chlorine, taste, odour (CTO); volatile organic compounds (VOC).

Average life-span: 3 months.

Maintenance: none.

Remark - Use a pre-filter to protect the cartridge.





LA cartridges are available in a variety of:

CONFIGURATIONS:

- SX standard configuration double open end (DOE) available for every height and diameter.
- BX proprietary configuration with double o-ring collar 45 mm, suitable to PLUS 3P BX housings, DP housings, K DP housings.

MODELS:

- LA MIGNON series 5"M OD 1.77" ID 0.71, SX configuration.
- LA series from 5" to 20" OD 2.40" ID 1.10", SX, BX configurations.

VARIANTS AVAILABLE ON MINIMUM QUANTITY:

- LA-Ag models with silver impregnated coconut GAC for bacteriostatic effect.

CERTIFICATIONS additio Conform D.M. 25/2012



LA cartridges are tested and certified under the most stringent procedures worldwide, in compliance with DM 25 (Italy) and EAC (Russia).

FLOW RATE vs PRESSURE DROP Δp

Tests carried on 10" elements type **LA 10 SX**. Testing mode: 20°C, 3 BAR

